
	Lineas de Perforación	POF	Doblada al centro	Fecha: 28 JUL 2023
	Perforation Lines	POF	Centerfold	Revisión: 0-07/24


1 Hasta 8" (200 mm) // 2 lineas: a 3" (75 mm) del doblaz primer linea y 2" siguiente linea.

Up to 8" (200 mm) // 2 lines: at 3" (75mm) from centerfold first line and 2" between following line.




2 De 9" (225 mm) hasta 18" (450 mm) // 3 lineas: a 3" (75 mm) del doblaz primer linea y 2" siguientes lineas.

From 9" (225 mm) up to 18" (450 mm) // 3 lines: at 3" (75mm) from centerfold first line and 2" between following lines.



3 De 19" (475 mm) hasta 26" (650 mm) // 4 lineas: a 3" (75 mm) del doblaz primer linea y 2" siguientes lineas.

From 19" (475 mm) up to 26" (650 mm) // 4 lines: at 3" (75mm) from centerfold first line and 2" between following lines.



4 De 27" (675 mm) hasta 40" (1000 mm) // 5 lineas: a 3" (75 mm) del doblaz primer linea y 2" siguientes lineas.

From 27" (675 mm) up to 40" (1000 mm) // 5 lines: at 3" (75mm) from centerfold first line and 2" between following lines.

